Digital Delay/Pulse Generator

DG535 — Digital delay and pulse generator (4-channel)



- · Four independent delay channels
- · Two fully-defined pulse channels
- 5 ps delay resolution
- <100 ps rms jitter</p>
- Adjustable amplitude and offset
- Delays up to 1000 seconds
- · 1 MHz maximum trigger rate
- · Standard GPIB interface
- Optional ±32 V outputs

· DG535 ... \$4195 (U.S. list)

DG535 Digital Delay/Pulse Generator-

The DG535 Digital Delay/Pulse Generator provides four precisely-timed logic transitions or two independent pulse outputs. The delay resolution on all channels is 5 ps, and the channel-to-channel jitter is typically 50 ps. Front-panel BNC outputs deliver TTL, ECL, NIM or variable level (–3 to +4 V) pulses into 50 Ω or high impedance loads. The high accuracy, low jitter, and wide delay range make the DG535 ideal for laser timing systems, automated testing, and precision pulse applications.

Delay Outputs

There are four delay output channels: A, B, C and D. The logic transitions of these outputs can be delayed from an internal or external trigger by up to 1000 seconds in 5 ps increments. The T0 pulse, which marks the beginning of a timing cycle, is generated by the trigger signal. The insertion delay between an external trigger and the T0 pulse is about 85 ns.

Delays for each channel may be "linked" to T0 or any of the other delay channels. For instance, you can specify the delays of the four channels as:

A = T0 + 0.00125000 B = A + 0.00000005 C = T0 + 0.10000000 D = C + 0.00100000



phone: (408)744-9040 www.thinkSRS.com

DG535 Digital Delay/Pulse Generator

In this case, when the A delay is changed, the B output will move with it. This is useful, for instance, when A and B specify a pulse and you want the pulse width to remain constant as the delay of the pulse is changed. Regardless of how the delay is specified, each delay output will stay asserted until 800 ns after all delays have timed out. The delays will then become unasserted, and the unit will be ready to begin a new timing cycle.

Pulse Outputs

In addition to the four delay outputs, there are four pulse output channels: AB, -AB, CD and -CD. The leading edge of the AB pulse coincides with the leading edge of the earlier of A or B, and the trailing edge of the AB pulse coincides with the leading edge of the later of B or A. For instance, in the previous example, a 50 ns pulse would appear at the AB output and a 1 ms pulse at CD. Pulses as short as 4 ns (FWHM) can be generated in this manner. The complementary outputs (-AB and -CD) provide a pulse with identical timing and inverted amplitude.

Output Amplitude Control

Each delay and pulse output has an independently adjustable offset and amplitude which can be set between -3 V and +4 V with 10 mV resolution. The maximum transition for each


output is limited to 4 V. In addition, you can also separately select 50 Ω or high impedance termination for each output. Preset levels, corresponding to standard logic families, can also be selected. TTL, NIM and ECL levels can each be set with a single key press.

Triggering

The DG535 can be triggered internally from 1 mHz to 1 MHz with 4-digit frequency resolution. External, single-shot and burst mode triggers are also supported. For power control applications, the DG535 can be synchronized to the AC line. An optional trigger inhibit input allows you to enable or disable triggering with a TTL level input signal.

±32 Volt Outputs

For applications requiring higher voltages, a rear-panel high voltage ($\pm 32~V$) option is available. This option provides five rear-panel BNCs which output 1 μs pulses at the transition times of the front-panel T0, A, B, C and D outputs. The high voltage option does not affect the function or the timing of the front-panel outputs. The amplitude of the rear-panel outputs is approximately $8\times$ the corresponding front-panel output, and the outputs are designed to drive 50 Ω loads. Since they can only drive an average current of 0.8 mA, charging and discharging the cable capacitance may be the most important



DG535 timing diagram




current limiting factor to consider when using them (assuming a high impedance load). In this case, the average current is: I=2Vtf/Z, where V is the pulse step size, t is the length of the cable in time (5 ns per meter for RG-58), f is the pulse repetition rate, and Z is the cable's characteristic impedance (50 Ω for RG-58).

Internal or External Timebase

Both internal and external references may be used as the timebase for the DG535. The internal timebase can be either the standard 25 ppm crystal oscillator timebase, or the optional 1 ppm temperature-compensated crystal oscillator (TCXO). The internal timebase is available as a 1 Vpp square wave on a rear-panel BNC. This output is capable of driving a 50 Ω load and can be used to provide a master timebase to other delay generators. Any external 10.0 MHz reference signal with a 1 Vpp amplitude can also be used as an external timebase.

Fast Rise and Fall Time Modules

External in-line modules are available to reduce the rise or fall time of the DG535 outputs to 100 ps. These modules use step



recovery diodes to speed up the rise time (option SRD1) or the fall time (option O4B). A bias tee (option O4C) allows these modules to be used with the optional rear-panel outputs to produce steps up to 15 V. For step amplitudes of less than 2.0 V, the fast transition time units should be attached directly to the front panel of the DG535.

Easy to Use, Easy to Program

All instrument functions can be accessed through a simple, intuitive, menu-based interface. Delays can be entered with the numeric keypad in either fixed-point or exponential notation, or by using the cursor keys to select and change

individual digits. The backlit 20-character LCD display makes it easy to view delay settings in all lighting conditions.

The DG535 comes standard with a GPIB (IEEE-488) interface. All instrument functions can be queried and set via the interface. You can even display the characters the DG535 has received over the interface on the front-panel LCD display. This can be valuable when debugging programs which send commands to the instrument.

Ordering Information

DG535	Delay/pulse generator w/ GPIB	\$4195
Option 02	±32 V rear panel outputs	\$650
Option 03	1 ppm TCXO timebase	\$350
Option 06	Trigger inhibit input	\$250
SRD1	100 ps rise time module	\$250
O4B	100 ps fall time module	\$250
O4C	Bias Tee (for 02 & SRD1 or O4B)	\$100
O5	Dual rack mount tray	\$150
	•	



DG535 rear panel (with Opt. 02)



DG535 Specifications

Delays

Channels Four independent delay outputs Range 0 to 999.999,999,999,995 seconds

Resolution 5 ps

Accuracy 1500 ps+timebase error × delay Timebase Standard: 25 ppm crystal oscillator Optional: 1 ppm TCXO (opt. 03)

External: 10.0 MHz reference input

Foo

RMS jitter $<100 \text{ ps} + (10^{-8} \times \text{delay})$

Trigger delay (typ.) 85 ns (ext. trigger to T0 output)

External Trigger

Rate DC to $1/(1 \mu s + longest delay)$

Threshold $\pm 2.56 \, \text{VDC}$ Resolution $10 \, \text{mV}$

Slope Trigger on rising or falling edge

Impedance $1 M\Omega + 40 pF \text{ or } 50 \Omega$

Internal Rate Generator

Rate Single shot, 0.001 Hz to

1.000 MHz, or line

Resolution Four digits, 0.001 Hz below 10 Hz

Accuracy Same as timebase Jitter 1:10,000

Settling <2 seconds for any rate change Burst mode 2 to 32766 pulses per burst at

integer multiples (4 to 32767) of the

trigger period

Outputs

Load 50Ω or high impedance

Rise time 2 to 3 ns (typ.)

Slew rate 1 V/ns

Overshoot <100 mV + 10 % of pulse amplitude Levels TTL: 0 to 4 VDC (normal or inverted)

> ECL: -1.8 to -0.8 VDC (normal or inverted) NIM: -0.8 to 0.0 VDC (normal or inverted) VAR: Adjustable offset and amplitude between -3 and +4 VDC

with 10 mV resolution. 4 V maximum transition.

Accuracy ±(50 mV + 3 % of pulse amplitude)
Option 02 Rear-panel 1 us pulses corresponding

to T0, A, B, C, D outputs with nominal amplitude of 8× the frontpanel outputs (1 kHz rep. rate). Output level is reduced by 2 V/mA of additional average output current.

Fast Rise Time (opt. SRD1)

Output amplitude +0.5 to 2.0 VDC Output offset +0.8 VDC (typ.)

Transition time

Rise (20/80%) 100 ps (max.) Fall (20/80%) 2000 ps (max.)

Pulse aberrations

Foot 4% (typ.) Ring $\pm 5\%$ (typ.)

Fast Fall Time (opt. O4B)

Output amplitude -0.5 to -2.0 VDC Output offset +0.8 VDC (typ.)

Transition time

Rise (20/80%) 2500 ps (max.) Fall (20/80%) 100 ps (max.)

Pulse aberrations

Foot 4% (typ.) Ring $\pm 5\%$ (typ.)

General

Display backlit 20-character LCD

Computer interface GPIB (IEEE-488). All instrument

functions and settings may be controlled over the interface bus. Interface queue can be viewed from

the front panel.

Dimensions $8.5" \times 4.75" \times 14"$ (WHD)

Weight 10 lbs.

Power 70 W, 100/120/220/240 VAC,

50/60 Hz

Warranty One year parts and labor on defects

in materials and workmanship